Motion Reference Unit MRU-PD



- 3-in-1 solution: MRU + DGPS/RTK + HDT
- Kongsberg/Seatex, SMC & TSS data formats*
- Compatible with SBES/MBES
- Input from DVL Doppler Velocity Log
- IHO SP44 standard compliant
- DGPS/RTK Position accuracy
- IP-67 or Subsea Enclosure
- 5 cm Heave accuracy
- 5 cm Surge & Sway accuracy
- 0.05 deg Heading accuracy
- 0.02 deg Pitch and Roll accuracy
- 0.005 m/sec² Acceleration accuracy
- 0.0002 deg/sec Angular rate accuracy
- NMEA 0183, TSS1 output data format






Inertiallabs MRU





Inertial Labs has developed a professional version of **Motion Reference Units (MRU-PD)** to meet the requirements from marine and hydrographic applications. The **MRU-PD** is an enhanced, high-performance strapdown Motion Sensor – affordable solution for survey, that determines Pitch & Roll, Heave, Sway, Surge, Accelerations, Angular rates, Heading, Velocity and Positions for any device on which it is mounted.



The Inertial Labs MRU-PD Motion Reference Units utilizes high precision, dual antenna GNSS receiver with DGPS and RTK positions accuracy, solid state 3-axes each of precision accelerometers, magnetometers, gyroscopes and barometric sensors to provide accurate Positions, Heading, Heave, Sway, Surge, Pitch and Roll of the device under measure. Integration of very low noise gyroscopes output provides high frequency, real-time measurement of the Vessel, Ships, Helidecs, ROV, Marine antennas, Cranes rotation about all three rotational axes.

Through a combination of proven sector expertise and a continued investment in technological innovation, Inertial Labs delivers the optimum balance of price and performance ratio solutions for its customers.

KEY FEATURES AND FUNCTIONALITY

- ABS Design Assessed
- Kongsberg/Seatex, Teledyne and SMC data formats*
- State-of-the-art algorithms for Vessels, Ships, Active Heave Compensators, Cranes, Helideck, ROV, AUV, DP-1, DP-2, DP-3 Buoys, Echo Sounders, Offshore Platforms
- 3 cm Oceanix Nearshore Horizontal Position Accuracy, 1-0.05 m VERIPOS Horizontal Position Accuracy
- 0.02 deg RMS Pitch & Roll accuracy
- > 5% or 5 cm RMS Heave accuracy
- > NMEA 0183, TSS1 output data formats
- ROS, LabVIEW, HYPACK, QINSY & Inertial Explorer support
- > Environmentally sealed (IP67), compact design



Our **MRU**s featuring developed few micro g Bias in-run stability Micro Electro Mechanical System (MEMS)-based accelerometers. New generation of Inertial Labs 1 deg/hr Bias in-run stability MEMS-based gyroscopes are an ideal solution for demanding marine applications, with their electronic nature negating the problems associated with expensive mechanical gyro solutions, as well as those based on fiber optic (FOG) technology. Inertial Labs MEMS gyroscopes set the standard for the industry, with our high-end **MRU**s featuring gyros that enable sector-leading accuracy and reliability standards.

Measured Parameters		WAYPINT PRODUCTS GROUP
Heave, Surge, Sway (% / cm)	✓	QINSy
Pitch & Roll (deg)	✓	WPACA III POS
Precision Heading (HDT) (deg)	✓	HYPACA ::: ROS
Velocity (meters/sec)	✓	
DGPS / RTK Positions (cm) ROS, LabVIEW, HYPACK, QINSy, Novatel IE support	*	LabVIEW





MRU-PD Specifications


Parameter	Units	MRI	J-PD		
	Heave, Surge, Sway, Heading/Yaw, Pitch, Roll, Positions, Velocities, Accelerations, Angular				
Output signals	rates, Barometric data, PPS time				
Output data formats	Kongsberg/Seatex, Ship Motion Control SMC, Teledyne TSS*				
Input Signal		ity Log), External Stand Alone Magne			
Compatibility	SBES/MBES: Teledyne; R2Sonic; WAASP; Kongsberg; EdgeTech; NORBIT; IMAGENEX* HYPACK, QINSY, Novatel Inertial Explorer software* DP-1, DP-2, DP-3, AHC, HMS, Survey systems				
Update rate	Hz	1 200 (u	ser settable)		
Internal Data Logger		64 GB (optional)		
Heave, Surge, Sway	Units	MRU-PD			
Measurement range	meters	±300			
Resolution	meters		.01		
Real time accuracy, RMS	% (meters)	- 1	0.05)		
Post Processing accuracy, RMS	% (meters)		(0.02)		
Pitch and Roll	Units		U-PD		
Range: Pitch, Roll	deg	±90, ±180			
Angular Resolution	deg		005		
Static Accuracy	deg		.01		
Dynamic Accuracy	deg RMS	0.02			
Post processing accuracy	deg RMS		006		
Heading	Units		U-PD		
Range	deg		360		
Angular Resolution	deg		001		
Real time Static and Dynamic Accuracy	deg		ers baseline)		
Real time Static and Dynamic Accuracy	deg		ers baseline)		
Post processing accuracy	deg RMS		0.03		
Positions, Velocity and Timestamps	Units		U-PD		
Horizontal position accuracy (SBAS), RMS	meters		0.6		
Horizontal position accuracy (DGPS), RMS	meters	0.4			
Horizontal position accuracy (RTK), RMS	meters		.01		
Horizontal position accuracy (Oceanix Nearshore) (1), RMS	meters	0.03			
Horizontal position accuracy (VERIPOS) (1), RMS	meters		0.05		
Horizontal position accuracy (PPK), RMS	meters	0.005			
GNSS Velocity accuracy, RMS	meters/sec	<0.03			
IMU Velocity accuracy, RMS PPS accuracy	meters/sec*√hr	<0.009			
	nano seconds Units	20			
Gyroscopes		MRU-PD			
Measurement range	deg/sec deg/hr	±450			
Bias in-run stability (RMS, Allan Variance)	deg/sec√Hz	1			
Accelerometers Noise density	Units	0.004 MRU-PD			
Measurement range	g	#8			
Bias in-run stability (RMS, Allan Variance)	mg	0.005			
Noise density	mg√Hz	0.005			
Pressure	Units	MRU-PD			
Measurement range	hPa	300 – 1100			
Bias in-run stability (RMS, Allan Variance)	Pa	2			
Noise density	Pa/√Hz	0.8			
Environment	Units	MRU-PD			
Operating temperature	deg C	-40 to +70			
Storage temperature	deg C	-50 to +85			
MTBF	hours	100,000			
Compliance to EMCD, immunity/emission		IEC 60945/EN 60945			
Electrical	Units	MRU-PD			
Supply voltage	V DC	9 to 36			
Power consumption	Watts	5 (6 with data logger)			
Output Interface	-	RS-232 / RS-422 / Ethernet / CAN			
Output data format	_	NMEA 0183, TSS-1, Binary ASCII characters			
Physical	MRU-PD (IP-67)	MRU-PDS (Subsea)			
Size	Units mm	120 x 50 x 53	245 x 140 x 115		
Weight	kg	0.320	6.5		
		•			

⁽¹⁾ Requires a subscription to a Oceanix data service, contact Inertial Labs for more information.






MRU-PD (IP-67) mechanical interface drawing



MRU-PDS (Subsea) mechanical interface drawing







MRU-PD Datasheet Rev. 3.2

Notes:

- All dimensions are in millimeters.
- All dimensions within this drawing are subject to change without notice. Customers should obtain final drawings before designing any interface hardware.
- Data connector type: Binder Series 723. Male receptacle, shielded, rear-mounting
- GNSS connector type: TNC-Female

MRU-PD and MRU-PDS part numbers description									
Model MRU-PD MRU-PDS	Gyro G450	Accel A8	Calibration TGA TMGA (optional)	Connector C3 C13	Color B S	Data Logger S64 (optional)	GNSS Receiver 07720	Version VD4 VD42 VD43 VD49 VD9	Interface 1245

Example: MRU-PD-G450-A8-TGA-C3-B-S64-07720-VD9.1245


Description:

- MRU-PD/MRU-PDS: Dual Antenna, Professional version of Motion Reference Unit (Heave, Surge, Sway, Pitch, Roll, High precision Heading, Position and Velocity Sensor)
- G450: Gyroscopes measurment range = \pm 450 deg/sec
- A8: Accelerometers measurement range = ± 8 g
- TGA: Gyroscopes and Accelerometers
- TMGA: Gyroscopes, Accelerometers, Embedded Fluxgate Magnetic Compass (optional)
- C3: 24 pins connector (IP-67)
- C13: 20 pin subsea connector
- B: Black color of enclosure (IP-67)
- S: Silver color (subsea version)
- S64: 64GB embedded Data Logger (optional)
- 07720: Dual Antenna GNSS receiver
- VD4: GPS L1/L2, SBAS, Dual antenna Heading, DGPS, (40 cm position accuracy)
- VD42: GPS L1/L2, GLONASS L1/L2, SBAS, DGPS, Dual antenna Heading RTK (1 cm position accuracy)
- VD43: GPS L1/L2, GLONASS L1/L2, Dual antenna Heading, SBAS, DGPS, 20 Hz positions
- VD49: GPS L1/L2, GLONASS L1/L2, NavIC (IRNSS), Dual antenna Heading, SBAS, DGPS, 20 Hz positions; 20 Hz GNSS
- VD9: GPS L1/L2, GLONASS L1/L2, BEIDOU B1/B2, GALILEO E1/E5, QZSS L1/L5, DGPS, RTK, Dual antenna Heading, 20 Hz measurements, 20 Hz positions
- .1245: RS-232, RS-422, CAN, Ethernet






IMU Center Diagram



DIMENSIONS ARE IN MILLIMETERS

All dimensions within this drawing are subject to change without notice. Customers should obtain final drawings before designing any interface hardware.

Inertial Labs Motion Reference Units (MRU) can be easily integrated into existing systems using the following bracket.



^{*} Trademark Legal Notice: All product names, logos, and brands are property of their respective owners. All company, product and service names used in this document are for identification purposes only. Use of these names, logos, and brands does not imply endorsement. Kongsberg/Seatex, Ship Motion Control SMC, Teledyne TSS, R2Sonic, WAASP, EdgeTech, NORBIT, IMAGENEX, HYPACK, QINSY, Novatel Installates or its respective owners, registered or used in many jurisdictions worldwide.